### **Double Wall Swivel Fitting**





## 03/08

### **Features**

*Pipe* 

- Crush and puncture resistant
- Semi-smooth liner facilitates ease of installation
- Saves time and money
- No buried joints
- Double Wall Construction

# Air Valve Test Jumper Stabilizer Bar Shear Valve Braided SS Flex Connector 1.5" Tee Fitting (STF-1515) DPC Jumper Tube Double Entry Boot with Test Port 1.5" DW Coupling

### Double Wall Swivel fittings (DPC's) are a proven coupling and fitting system designed exclusively for use with FlexWorks piping

Double Wall Swivel couplings and fittings are of a double wall design and are used to interconnect FlexWorks flexible piping.

The pipe connection system includes an internally expanded stainless steel coupling attached to the end of a FlexWorks pipe section. The swivel coupling has a smooth sealing face fitted with a viton ring gasket.

Double wall Swivel Couplings eliminate the need for cutting back the secondary jacket and rubber test boots. They have an integral interstitial access port for connector and test tubes. These double wall couplings permit higher interstitial testing pressures and eliminate added parts and labor costs.



## **Double Wall Swivel Fitting Ordering Specifications**

Part #	Application			
DPC-2150A	I.5" Double Wall Swivel Pipe Coupling, flat gasket			
DPC-2200A	2" Double Wall Swivel Pipe Coupling, flat gasket			

### **Double Wall Swivel Fitting**





### **Coupling Machine & Swage Kits**

Double wall pipe couplings require the use of an OPW-FCS coupling machine to internally expand the stainless steel fitting onto the end of a FlexWorks pipe section. Internally expanded couplings have a long, successful history of reliable performance.

There are multiple types of Coupling Machines available. Our Electronic Coupling Machines (CME-0110 and CME-0220) as well as our Remote Coupling Machine (CME-0110R) can couple Double wall couplings. Manually operated and Pneumatic Coupling Machines are also available (CMM-200 and CMP-200).

Swage Kits are required. Swages are used with the OPW Fueling Containment Systems Coupling Machine to internally expand the coupling onto the end of the flexible pipe section. There are a variety of coupling swage kits available.

use with OPW Coupling Machines:


Please see the chart below for the applicable Swage Kit product numbers required for



Electronic Coupling Machine (CME)



Pneumatic Coupling Machine (CMP)



Manually Operated Coupling Machine (CMM)

Fitting Type & Model No.	Coupling Machine Model						
		CME-0110	CME-0110R	CME-0220	CMM-200	CMP-200	
1.5" DW Swivel (DPC-2150)	Swage Kit Number	CSK-0150S	CSK-0150S	CSK-0150S	SBA2-0150	SBA2-0150	
2" DW Swivel (DPC-2200)		CSK-0200S	CSK-0200S	CSK-0200S	SBA2-0200	SBA2-0200	





### **OPW Fueling Containment Systems**

3250 US Highway 70 Business W.
Smithfield, NC 27577
Customer Service: I-800-422-2525
Customer Service Fax: I-800-421-3297
Literature Requests: I-919-934-2786 x204
www.opwfcs.com



Publication: DPC-0002 Issue Date: 06/07/13 Supercedes: 09/06/11